

TECHNICAL DATA SHEET

Part No. 156-01726
Article No. 156-01726
Type T50RBHMB



HellermannTyton Blind Hole Mount Cable Ties for threaded and nonthreaded holes offer an easy-to-use method for bundling and affixing cables. The two-piece design includes a heat-stabilized cable tie and formula-matched, 1/4" mount that features a low push-in force and aggressively resists pull out. Performs equally well in threaded or nonthreaded blind holes. Mount can slide along cable tie to adjust orientation if needed. Fastener can be removed from hole using a hex driver, ensuring reuse if desired.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Cable Tie	PA66HS
Material Foot Part	PA66HS
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	4000
Customs Number	3926909988

Description	Inside Serrated
Diameter (imperial)	0.25 "
Diameter (metric)	6.35 mm
Fixation Method	Blind Plug
Height (imperial)	0.736 "
Height (metric)	18.7 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.246 - 0.253 "
Mounting Hole Diameter (metric)	6.25 - 6.45 mm
Width (imperial)	0.31 "
Width (metric)	7.8 mm

