

TECHNICAL DATA SHEET

Part No. 156-01784
Article No. 156-01784
Type T50SMVCMOC7M180



The MOC 180 to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The clip's orientation allows the second routing to be assembled in the direction of the first routing. The swivel coupler allows the two routings to rotate independently of each other.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	1.14 "
Height (metric)	28.9 mm
Length (imperial)	0.46 "
Length (metric)	11.6 mm
Length 2 (imperial)	0.55 "
Length 2 (metric)	14.0 mm
Max. Bundle Diameter (imperial)	0.31 "
Max. Bundle Diameter (metric)	8.0 mm
Min. Bundle Diameter (imperial)	0.24 "
Min. Bundle Diameter (metric)	6.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Nominal Bundle Diameter (imperial)	0.28"
Nominal Bundle Diameter (metric)	7.0 mm

