

TECHNICAL DATA SHEET

Part No. 156-01948
Article No. 156-01948
Type MOC6FMOC5M180



The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	0.47 "
Height (metric)	12.0 mm
Length (imperial)	1.06 "
Length (metric)	26.87 mm
Length 2 (imperial)	0.61 "
Length 2 (metric)	15.4 mm
Max. Bundle Diameter (imperial)	0.27 "
Max. Bundle Diameter (metric)	6.8 mm
Max. Bundle Diameter 2 (imperial)	0.22 "
Max. Bundle Diameter 2 (metric)	5.5 mm
Min. Bundle Diameter (imperial)	0.22 "
Min. Bundle Diameter (metric)	5.5 mm
Min. Bundle Diameter 2 (imperial)	0.16 "
Min. Bundle Diameter 2 (metric)	4.0 mm

HF ✓

RoHS ✓