

# TECHNICAL DATA SHEET

**Part No.** 156-02015  
**Article No.** 156-02015  
**Type** MOC8FMOC16M180



The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	2000
<b>Carton Qty.</b>	2000
<b>Customs Number</b>	3926909988

<b>Height (imperial)</b>	0.90 "
<b>Height (metric)</b>	22.9 mm
<b>Length (imperial)</b>	1.74 "
<b>Length (metric)</b>	44.12 mm
<b>Length 2 (imperial)</b>	0.90 "
<b>Length 2 (metric)</b>	22.9 mm
<b>Max. Bundle Diameter (imperial)</b>	0.35 "
<b>Max. Bundle Diameter (metric)</b>	9.0 mm
<b>Max. Bundle Diameter 2 (imperial)</b>	0.72 "
<b>Max. Bundle Diameter 2 (metric)</b>	18.3 mm
<b>Min. Bundle Diameter (imperial)</b>	0.28 "
<b>Min. Bundle Diameter (metric)</b>	7.0 mm
<b>Min. Bundle Diameter 2 (imperial)</b>	0.55 "
<b>Min. Bundle Diameter 2 (metric)</b>	14.0 mm

