

# TECHNICAL DATA SHEET

**Part No.** 156-02201  
**Article No.** 156-02201  
**Type** MOC26FMOC7M180



The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                        |
| <b>Flammability</b>          | UL 94 HB                                                                 |
| <b>Halogen Free</b>          | Yes                                                                      |
| <b>UV Resistant</b>          | Yes                                                                      |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                               |
| <b>Color</b>                 | Black (BK)                                                               |
| <b>Pkg. Qty.</b>             | 2000                                                                     |
| <b>Carton Qty.</b>           | 2000                                                                     |
| <b>Customs Number</b>        | 3926909988                                                               |

|                                          |          |
|------------------------------------------|----------|
| <b>Height (imperial)</b>                 | 1.61 "   |
| <b>Height (metric)</b>                   | 41.0 mm  |
| <b>Length (imperial)</b>                 | 2.05 "   |
| <b>Length (metric)</b>                   | 51.99 mm |
| <b>Length 2 (imperial)</b>               | 1.10 "   |
| <b>Length 2 (metric)</b>                 | 28.0 mm  |
| <b>Max. Bundle Diameter (imperial)</b>   | 1.14 "   |
| <b>Max. Bundle Diameter (metric)</b>     | 29.0 mm  |
| <b>Max. Bundle Diameter 2 (imperial)</b> | 0.31 "   |
| <b>Max. Bundle Diameter 2 (metric)</b>   | 8.0 mm   |
| <b>Min. Bundle Diameter (imperial)</b>   | 0.91 "   |
| <b>Min. Bundle Diameter (metric)</b>     | 23.0 mm  |
| <b>Min. Bundle Diameter 2 (imperial)</b> | 0.24 "   |
| <b>Min. Bundle Diameter 2 (metric)</b>   | 6.0 mm   |

HF ✓

RoHS ✓