

TECHNICAL DATA SHEET

Part No. 156-02226
Article No. 156-02226
Type T50REC5A



HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

| | |
|------------------------------|--|
| Material | Polyamide 6.6, high impact modified, heat and UV-stabilized, proprietary blend (PA66HIRHSUVR5), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Cable Tie | PA66HIRHSUV |
| Material Foot Part | PA66HIRHSUVR5 |
| Operating Temperature | -40°F to +239°F (-40°C to +115°C), -40°F to +230°F (-40°C to +110°C) |
| Flammability | UL 94 HB |
| UV Resistant | Yes |
| Use Conditions | For Indoor and Outdoor Use |
| Color | Black (BK) |
| Pkg. Qty. | 100 |
| Carton Qty. | 4000 |
| Customs Number | 3926909988 |

| | |
|---|---------------|
| Fixation Method | Edge Clip |
| Height (imperial) | 0.61 " |
| Height (metric) | 15.5 mm |
| Length (imperial) | 8.0 " |
| Length (metric) | 203.2 mm |
| Length 2 (imperial) | 0.55 " |
| Length 2 (metric) | 14.0 mm |
| Max. Bundle Diameter (imperial) | 1.97 " |
| Max. Bundle Diameter (metric) | 50.0 mm |
| Min. Tensile Strength (imperial) | 20 lbs |
| Min. Tensile Strength (metric) | 89 N |
| Panel Thickness (imperial) | 0.04 - 0.12 " |
| Panel Thickness (metric) | 1.0 - 3.0 mm |
| Thickness (imperial) | 0.05 " |
| Thickness (metric) | 1.2 mm |
| Width (imperial) | 0.18 " |
| Width (metric) | 4.6 mm |

