

TECHNICAL DATA SHEET

Part No. 156-02241
Article No. 156-02241
Type T50SVCMOC7M



The MOC to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The swivel coupler allows the two routings to rotate independently of each other.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	1.0 "
Height (metric)	25.4 mm
Length (imperial)	0.52 "
Length (metric)	13.2 mm
Length 2 (imperial)	0.55 "
Length 2 (metric)	14.0 mm
Max. Bundle Diameter (imperial)	0.31 "
Max. Bundle Diameter (metric)	8.0 mm
Min. Bundle Diameter (imperial)	0.24 "
Min. Bundle Diameter (metric)	6.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Nominal Bundle Diameter (imperial)	0.28"
Nominal Bundle Diameter (metric)	7.0 mm

