

# TECHNICAL DATA SHEET

**Part No.** 156-02352  
**Article No.** 156-02352  
**Type** MOC14FMOC22M



The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                        |
| <b>Flammability</b>          | UL 94 HB                                                                 |
| <b>Halogen Free</b>          | Yes                                                                      |
| <b>UV Resistant</b>          | Yes                                                                      |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                               |
| <b>Color</b>                 | Black (BK)                                                               |
| <b>Pkg. Qty.</b>             | 1000                                                                     |
| <b>Carton Qty.</b>           | 1000                                                                     |
| <b>Customs Number</b>        | 3926909988                                                               |

|                                          |         |
|------------------------------------------|---------|
| <b>Height (imperial)</b>                 | 1.44 "  |
| <b>Height (metric)</b>                   | 36.5 mm |
| <b>Length (imperial)</b>                 | 2.19 "  |
| <b>Length (metric)</b>                   | 55.6 mm |
| <b>Length 2 (imperial)</b>               | 1.17 "  |
| <b>Length 2 (metric)</b>                 | 29.7 mm |
| <b>Max. Bundle Diameter (imperial)</b>   | 0.62 "  |
| <b>Max. Bundle Diameter (metric)</b>     | 15.8 mm |
| <b>Max. Bundle Diameter 2 (imperial)</b> | 0.98 "  |
| <b>Max. Bundle Diameter 2 (metric)</b>   | 25.0 mm |
| <b>Min. Bundle Diameter (imperial)</b>   | 0.51 "  |
| <b>Min. Bundle Diameter (metric)</b>     | 13.0 mm |
| <b>Min. Bundle Diameter 2 (imperial)</b> | 0.79 "  |
| <b>Min. Bundle Diameter 2 (metric)</b>   | 20.0 mm |
| <b>Width (metric)</b>                    | 12.0 mm |

