

TECHNICAL DATA SHEET

Part No. 156-02384
Article No. 156-02384
Type T50SMVCLOC5-9



HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHS
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Height (imperial)	1.08 "
Height (metric)	23.6 mm
Length (imperial)	8.3 "
Length (metric)	210.0 mm
Length 2 (imperial)	0.73 "
Length 2 (metric)	18.6 mm
Max. Bundle Diameter (imperial)	0.35 "
Max. Bundle Diameter (metric)	9.0 mm
Min. Bundle Diameter (imperial)	0.2 "
Min. Bundle Diameter (metric)	5.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Nominal Bundle Diameter (imperial)	0.20 " - 0.35 "
Nominal Bundle Diameter (metric)	5.0 mm - 9.0 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

HF ✓

RoHS ✓