

TECHNICAL DATA SHEET

Part No. 156-02592
Article No. 156-02592
Type T120RFT12SET



These two-piece fasteners offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.

Material	Polyamide 4.6 (PA46)
Material Cable Tie	PA46
Material Foot Part	PA46
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	1.17 "
Height (metric)	29.70 mm
Length (imperial)	15.0 "
Length (metric)	385.0 mm
Max. Bundle Diameter (imperial)	4.13 "
Max. Bundle Diameter (metric)	105.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Hole Diameter (imperial)	0.46 - 0.49 "
Mounting Hole Diameter (metric)	11.6 - 12.4 mm
Panel Thickness (imperial)	0.02 - 0.43 "
Panel Thickness (metric)	0.6 - 11.0 mm
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

