

TECHNICAL DATA SHEET

Part No. 156-02648
Article No. 156-02648
Type IRCDFTOVAL



The Fir Tree Mount Ratchet Clamp offers versatility when managing wires, cables and hoses. Integrated fir tree means no additional hardware is needed for securing to a hole. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal of cables simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the mounting surface.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	200
Carton Qty.	200
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Length (imperial)	1.37 "
Length (metric)	34.8 mm
Max. Bundle Diameter (imperial)	2 "
Max. Bundle Diameter (metric)	50.8 mm
Min. Bundle Diameter (imperial)	1.42 "
Min. Bundle Diameter (metric)	36.01 mm
Min. Tensile Strength (imperial)	100 lbs
Mounting Hole Diameter (imperial)	0.28 x 0.47 "
Mounting Hole Diameter (metric)	7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Width (imperial)	1.37 "
Width (metric)	34.9 mm

