

TECHNICAL DATA SHEET

Part No. 156-02705
Article No. 156-02705
Type T50RSRAH6.5D1.4TSD



HellermannTyton sealed clips and ties are constructed of engineered nylon with a dual TPE (thermo plastic elastomer) seal. The combination of dual seal and engineered arrowhead provide superior sealing performance for applications where protection from moisture and debris is essential.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Thermoplastic Elastomer (TPE)
Operating Temperature	-40°F to +230°F (-40°C to +110°C), -40°F to +221°F (-40°C to +105°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK), Gray (GY)
Pkg. Qty.	2000
Carton Qty.	1000 box
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.59 "
Height (metric)	15.08 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 " (HEXAGONAL), 0.26 "
Mounting Hole Diameter (metric)	6.35 mm (hexagonal), 6.5 mm
Panel Thickness (imperial)	0.05 - 0.07 "
Panel Thickness (metric)	1.2 - 1.8 mm
Width (imperial)	0.87 "
Width (metric)	22.3 mm

