

TECHNICAL DATA SHEET

Part No. 156-02987
Article No. 156-02987
Type T120RCP6M6FT6.5SET



These heavy duty cable tie mounts, secured with mechanical fasteners, include an anti-rotation pin that keeps the mount and harness assembly in position during the torquing of the bolt or nut. They provide an attachment point for securing and routing a single bundle. The mounts provide the highest level of fastening for critical cable security.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHSUV
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	1.11 "
Height (metric)	28.22 mm
Length (imperial)	15.0 "
Length (metric)	385.0 mm
Max. Bundle Diameter (imperial)	4.13 "
Max. Bundle Diameter (metric)	105.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Screw Type	M6 Screw
Stud Diameter (imperial)	0.24 "
Stud Diameter (metric)	6.0 mm
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

HF✓

RoHS✓