

TECHNICAL DATA SHEET

Part No. 156-03000
Article No. 156-03000
Type IRCBSTRUT



The Quick2Clamp offers ultra-fast installation and versatility for managing conduit, tubing and cables. The built-in strut mount attaches with a simple twist. The one-piece design makes it simple to install without tools. Robust, adjustable clamp closes by hand to the desired diameter. A release feature allows easy and nondestructive maintenance simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the strut.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	200
Carton Qty.	200
Customs Number	3926909988

Fixation Method	1-5/8 " strut attachment
Length (imperial)	3.15 "
Length (metric)	79.9 mm
Max. Bundle Diameter (imperial)	0.77 "
Max. Bundle Diameter (metric)	19.5 mm
Max. Static Load (imperial)	70 lbs
Maximum Static Load (N)	311 N
Min. Bundle Diameter (imperial)	0.5 "
Min. Bundle Diameter (metric)	12.7 mm
Width (imperial)	1.37 "
Width (metric)	34.81 mm

