

TECHNICAL DATA SHEET

Part No. 156-03233
Article No. 156-03233
Type T50RMAGCTM15LSET



Magnetic cable tie mount with T50R tie routes bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle to the mount with the cable tie and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Material	Neodymium alloy 35M (NDFEB35M), Polyacetal (POM), Steel (ST), Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Halogen Free	Yes
Plenum Rating	AH-2
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	100 Pieces
Customs Number	8505110070

Diameter (imperial)	0.91 "
Diameter (metric)	23.2 mm
Fixation Method	Magnet
Height (imperial)	0.41 "
Height (metric)	10.5 mm
Magnetic pull strength (lb/ft)	15 lbf-ft
Magnetic pull strength (N)	66 N
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50 mm
Max. Cable Tie Width (imperial)	0.23 "
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222 N
Rotation (°)	360 °
Thickness (imperial)	0.047 "
Thickness (metric)	1.2 mm

