

TECHNICAL DATA SHEET

Part No. 156-03335
Article No. 156-03335
Type T50RUPBM9SET



This button head mount includes a cable tie to secure cables and wire bundles to panels. Once placed through a panel hole, installers can insert the cable tie through the mount on the panel's opposite side. The button head mount is designed to fit pre-stamped oval hole sizes 7x10 mm, 7x12 mm, 8.5x16 mm, 9x12 mm and 9x14 mm with zero insertion force.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.29 "
Cable Tie Head Length (metric)	7.3 mm
Cable Tie Head Width (imperial)	0.30 "
Cable Tie Head Width (metric)	7.6 mm
Description	Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width
Fixation Method	Button Head
Height (imperial)	0.53 "
Height (metric)	13.40 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.28 x 0.39 ", 0.34 x 0.63 ", 0.35 x 0.47 ", 0.35 x 0.55 ", 0.35 ", 0.33 "
Mounting Hole Diameter (metric)	7.0 x 10.0 mm, 9.0 x 12.0 mm, 9.0 x 14.0 mm, 8.5 x 16.0 mm, 8.5 mm, 9.0 mm
Panel Thickness (imperial)	0.12 "
Panel Thickness (metric)	3.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.67 "
Width (metric)	17.0 mm



