

TECHNICAL DATA SHEET

Part No. 156-03366
Article No. 156-03366
Type T120RCOUPLER



The Coupler is the simple way to connect two cable ties for a parallel routing of two bundles. This special design allows the ties 90 degrees of rotation. This is ideal for all applications where the cable, pipe or hose should move flexible in relation to the fixing point. The Coupler can be used with one or two cable ties. This allows easily subsequent installation or replacements of further cables, pipes or hose.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PA66HIRHS
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Foot Part Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	500 Pieces
Customs Number	3926909988

For Cable Tie Series	T120
Height (imperial)	0.59 "
Height (metric)	14.9 mm
Length (imperial)	14.96 "
Length (metric)	390.0 mm
Max. Bundle Diameter (imperial)	4.13 "
Max. Bundle Diameter (metric)	105.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

