

TECHNICAL DATA SHEET

Part No. 156-03596
Article No. 156-03596
Type T120RLOC25-30-SET



HellermannTyton's two-piece cable tie assembly offers dual bundle routing. The clamp portion securely locks completely around one bundle, while the cable tie creates a secure solution for a second bundle.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000 Pieces
Customs Number	3926909988

Attaches to Diameter (imperial)	0.98 - 1.18 "
Attaches to Diameter (metric)	25.0 - 30.0 mm
Length (imperial)	15.2 "
Length (metric)	387.0 mm
Max. Bundle Diameter (imperial)	1.18 "
Max. Bundle Diameter (metric)	30.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Width (imperial)	0.59 "
Width (metric)	15.0 mm

RoHS