

TECHNICAL DATA SHEET

Part No. 156-03942
Article No. 156-03942
Type LPT50RSRAH6.5D1.4TSD



HellermannTyton sealed arrowhead mount and tie are constructed of engineered nylon with a dual TPE (thermo plastic elastomer) seal. The combination of dual seal and engineered arrowhead provide superior sealing performance for applications where protection from moisture and debris is essential. Low profile cable tie features a compact, contoured head designed to use less space in confined areas and reduce protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. The outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles while offering high tensile strength and low insertion force. This mount is sold as an assembly with the cable tie.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK), Gray (GY)
Pkg. Qty.	500
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.55 "
Height (metric)	13.85 mm
Length (imperial)	7.7 "
Length (metric)	194.6 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.27 ", 0.24 - 0.26 " (HEXAGONAL)
Mounting Hole Diameter (metric)	6.1 - 6.9 mm, 6.15 - 6.55 mm (hexagonal)
Panel Thickness (imperial)	0.05 - 0.07 "
Panel Thickness (metric)	1.2 - 1.8 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS