

TECHNICAL DATA SHEET

Part No. 156-03950
Article No. 156-03950
Type T120R2XDHVSDOS12X17



HellermannTyton's Fir Tree Mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. They are optimized for up to 3-to-1 extraction versus insertion force to make assembly fast and easy. These mounts are sold unassembled.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHSUV
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500 Pieces
Customs Number	3926909988

Height (imperial)	1.24 "
Height (metric)	31.6 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	4.13 "
Max. Bundle Diameter (metric)	105.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Hole Diameter (imperial)	0.47 x 0.67 "
Mounting Hole Diameter (metric)	12.0 x 17.0 mm
Panel Thickness (imperial)	0.02 - 0.19 "
Panel Thickness (metric)	0.6 - 4.73 mm
Width (imperial)	1.26 "
Width (metric)	32 mm

