

TECHNICAL DATA SHEET

Part No. 156-03972
Article No. 156-03972
Type T50RCPCM67DTSSET



Part of our sustainable line of products, the ReSource product family features solutions made from excess plastic left over from the manufacturing process or from consumers. This cable tie mount is made from 100 percent postindustrial recycled plastic. It is secured with a mechanical fastener and includes an anti-rotation pin that keeps the mount and harness assembly in position while torquing the bolt or nut. It provides an attachment point for securing and routing a single bundle. The mount provides the highest level of fastening for critical cable security.

Material	Polyamide 6.6 recycled, high impact modified, heat stabilized (PA66HIRHS(REC))
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Flammability	UL 94 HB
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	0.061 "
Height (metric)	15.5 mm
Length (imperial)	8.0 "
Length (metric)	202.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Screw Type	1/4" (M6) Screw
Stud Diameter (imperial)	0.24 "
Stud Diameter (metric)	6.0 mm
Width (imperial)	0.79 "
Width (metric)	20.0 mm

