

TECHNICAL DATA SHEET

Part No. 156-04065
Article No. 156-04065
Type T50RX2DUALSDFT6.5A



These two-piece self-affixing cable ties are supplied ready assembled and offer a simple and versatile method of bundling and fastening cables. The deep-hole anchor will easily push into blind holes with or without thread and offers a very secure attachment. The two-piece design enables the head of the tie to be oriented to the required position to ease assembly, while the disc on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Orange (OG), High Voltage (HV), Black (BK)
Pkg. Qty.	500
Carton Qty.	500 Pieces
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.80 "
Height (metric)	20.5 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.23 "
Panel Thickness (metric)	0.6 - 6.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.46 "
Width (metric)	11.7 mm

HF ✓

RoHS ✓