

TECHNICAL DATA SHEET

Part No. 156-04196
Article No. 156-04196
Type IRCBATI



The ATI (Array Technologies) Ratchet Clamp attaches to Array Technologies torque tubes without any additional hardware. It offers one-handed, toolless simplicity and size versatility for managing wires and cables on solar modules. The robust design and solar-optimized materials make it ideal for heavy duty, outdoor applications. The one-piece adjustable clamp can be closed by hand to the desired diameter, replacing multiple sizes for single-diameter fasteners. The integrated release feature enables easy and nondestructive removal of cables by inserting a flat-head screwdriver. This allows the clamp to be reused without removing it.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Stainless Steel (SS304)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	200
Carton Qty.	200 box
Customs Number	3926909988

Fixation Method	Mounting Hanger
Length (imperial)	3.15 "
Length (metric)	79.9 mm
Max. Bundle Diameter (imperial)	0.77 "
Max. Bundle Diameter (metric)	19.6 mm
Min. Bundle Diameter (imperial)	0.5 "
Min. Bundle Diameter (metric)	12.7 mm
Width (imperial)	1.37 "
Width (metric)	34.8 mm

