

TECHNICAL DATA SHEET

Part No. 156-04211
Article No. 156-04211
Type T120SFTM8SET



HellermannTyton's fir tree mount provides a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. It is sold as an unassembled set with the cable tie.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHSUV
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.90 "
Height (metric)	22.77 mm
Length (imperial)	9.0 "
Length (metric)	229.0 mm
Max. Bundle Diameter (imperial)	2.17 "
Max. Bundle Diameter (metric)	55.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Hole Diameter (imperial)	0.24 - 0.26 "
Mounting Hole Diameter (metric)	6.0 - 6.9 mm, M8 Threaded
Panel Thickness (imperial)	0.02 - 0.24 "
Panel Thickness (metric)	0.6 - 6.0 mm
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

RoHS✓