

TECHNICAL DATA SHEET

Part No. 156-04247
Article No. 156-04247
Type SMF2MOC10MX2



These clips can be attached to the stud prior to installing the pipe or hose. The parts prefixed with an 'I' can be interlocked together giving a greater choice of installation options or mounted onto a 5 mm 'T' stud or the IAHC type of Automatic Harness Clips.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Height (imperial)	1.14 "
Height (metric)	28.9 mm
Height 2 (imperial)	0.7 "
Height 2 (metric)	17.8 mm
Length (imperial)	2.36 "
Length (metric)	60.0 mm
Length 2 (imperial)	1.69 "
Length 2 (metric)	43.0 mm
Max. Bundle Diameter (imperial)	0.45 "
Max. Bundle Diameter (metric)	11.5 mm
Max. Bundle Diameter 2 (imperial)	0.45 "
Max. Bundle Diameter 2 (metric)	11.5 mm
Min. Bundle Diameter (imperial)	0.37 "
Min. Bundle Diameter (metric)	9.5 mm
Min. Bundle Diameter 2 (imperial)	0.37 "
Min. Bundle Diameter 2 (metric)	9.5 mm
Stud Diameter (imperial)	0.20 ";0.24 "
Stud Diameter (metric)	5.0 mm, 6.0 mm

