

TECHNICAL DATA SHEET

Part No. T50RTM25E0HSM4
Article No. 157-00001
Type T50RTM25E



Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.05 "
Height (metric)	1.3 mm
Length (imperial)	8.0 "
Length (metric)	203.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.25 - 7.0 mm
Panel Thickness (imperial)	0.09 - 0.50 "
Panel Thickness (metric)	2.3 - 13.9 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS 