

TECHNICAL DATA SHEET

Part No. 157-00054
Article No. 157-00054
Type T50ROSFT7X12U



Fir Tree Mounts offer a simple and easy-to-use method of bundling and mounting cables. The design of the fir tree ensures a secure and robust fit into panels with a 7.0–12.0mm holes and a thickness between 0.6 mm–4.0 mm. The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt. This can be applied by hand and tensioned with one of HellermannTyton's manual or pneumatic hand tools.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.41 "
Height (metric)	10.5 mm
Length (imperial)	8.5 "
Length (metric)	215.9 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.28 x 0.47 "
Mounting Hole Diameter (metric)	7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.16 "
Panel Thickness (metric)	0.6 - 4.0 mm
Thickness (imperial)	0.06 "
Thickness (metric)	1.5 mm
Width (imperial)	0.2 "
Width (metric)	5.08 mm

RoHS✓