

TECHNICAL DATA SHEET

Part No. 157-00130
Article No. 157-00130
Type T50ROSFT6SO12.5A



Offset cable ties route and position bundles away from a mounting hole. Rigid offset bar eliminates potential bending of wire or cables once installed. Multiple offset distances and fir tree sizes cover the majority of industry offset applications. The tie strap's outside serration design provides a smooth surface to protect soft bundles. HellermannTyton's one-piece mounting ties offer a complete solution by both bundling and mounting. Their ideal combination of high-specification materials and superior design suit the needs of complex applications.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.87 "
Height (metric)	22.10 mm
Length (imperial)	8.5 "
Length (metric)	215.9 mm
Length 2 (imperial)	0.49 "
Length 2 (metric)	12.5 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 " (HEXAGONAL), 0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 7.0 mm, 6.35 mm (hexagonal)
Offset Length (imperial)	0.49 "
Offset Length (metric)	12.5 mm
Panel Thickness (imperial)	0.02 - 0.26 "
Panel Thickness (metric)	0.6 - 6.65 mm
Width (imperial)	0.19 "
Width (metric)	5.1 mm

