

Technical data sheet

Article number:

157-00169

T50ROSFT6SO25B

Product Group	1-piece fixing ties with fir tree, with disc, with stand-off, for round holes
Product Family	With offset 12.5 and 25.0 mm
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, EVOcut, MK9P, MK9P w/ Upper air, MK10-SB, MK21, EVO7, EVO7SP, EVO7iSP, EVO9, EVO9SP, EVO9HT, EVO9i, EVO9iSP, EVO9iHT
Bundle Ø max.	50.0 mm
Bundle Ø min.	2.0 mm
CE Certification	No
Fixation Method	Fir tree for round holes
Flammability	UL 94 HB
for Hole Ø (FH)	6.1 - 7.0 mm, 6.35 mm (hexagonal)
Height (H)	22.3 mm
Length (L)	230.0 mm
Length (L2)	25.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C
Package Content	3000 pcs.
Package Content packed in	pack
Panel Thickness	0.6 - 6.65 mm
Panel Thickness max.	6.65 mm
Panel Thickness min.	0.6 mm
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	4.7 mm

RoHS ✓