

TECHNICAL DATA SHEET

Part No. 157-00187
Article No. 157-00187
Type T50SOSFT8-E2



Fir Tree Mounts offers a simple and easy to use method of bundling and mounting cables. The design of the fir tree ensures a secure and robust fit into panels with a round mounting hole between thicknesses between 0.03 - 0.28". The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt. The outside serrated tie can be applied by hand and tensioned with one of HellermannTyton's manual or pneumatic hand tools.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	2500
Customs Number	3926909988

Fixation Method	Fir Tree
Length (imperial)	6.5 "
Length (metric)	165.1 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	40.5 lbs
Min. Tensile Strength (metric)	180 N
Mounting Hole Diameter (imperial)	0.30 - 0.33 "
Mounting Hole Diameter (metric)	7.6 - 8.4 mm
Panel Thickness (imperial)	0.024 - 0.255 "
Panel Thickness (metric)	0.6 - 6.5 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

