

TECHNICAL DATA SHEET

Part No. 157-00197
Article No. 157-00197
Type T50ROSFT6S25SO



HellermannTyton's Off-Set Fir Tree Cable Tie and fixing offers a simple and easy to use method of bundling and fixing cables, the design of the fir tree ensures a positive and secure fixing into panels with thicknesses from .2" - .26" or threaded blind holes.

The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Length (imperial)	9.5 "
Length (metric)	242.2 mm
Length 2 (imperial)	0.98 "
Length 2 (metric)	25.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Offset Length (imperial)	0.98 "
Offset Length (metric)	25.0 mm
Panel Thickness (imperial)	0.02 - 0.15 "
Panel Thickness (metric)	0.6 - 3.75 mm
Width (imperial)	0.20 "
Width (metric)	5.1 mm

RoHS✓