

TECHNICAL DATA SHEET

Part No. 157-00205
Article No. 157-00205
Type T50ROSFTOVAL25A



One-piece cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	500
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Height (imperial)	0.52 "
Height (metric)	13.15 mm
Length (imperial)	9.03 "
Length (metric)	229.3 mm
Length 2 (imperial)	0.98 "
Length 2 (metric)	25.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222.4 N
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.26 x 0.49 ", 0.26 x 0.51 ", 0.28 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Offset Length (imperial)	0.98 "
Offset Length (metric)	25.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.35 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

RoHS ✓