

TECHNICAL DATA SHEET

Part No. 157-00295
Article No. 157-00295
Type T80ROSSB12U



Stud Mount Ties offer outstanding stud retention. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Material	Polyamide 4.6 (PA46)
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Brown (BN)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.70 "
Height (metric)	17.0 mm
Length (imperial)	8.6 "
Length (metric)	218.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	80 lbs
Min. Tensile Strength (metric)	355 N
Stud Diameter (imperial)	0.47 "
Stud Diameter (metric)	12.0 mm
Width (imperial)	0.93 "
Width (metric)	23.75 mm

RoHS 