

# TECHNICAL DATA SHEET

**Part No.** 157-00341  
**Article No.** 157-00341  
**Type** T80ROSLPSB8U



Mount features a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

<b>Material</b>	Polyamide 4.6 (PA46)
<b>Operating Temperature</b>	-40°F to +266°F (-40°C to +130°C)
<b>Flammability</b>	UL 94 V-2
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Brown (BN)
<b>Pkg. Qty.</b>	2000
<b>Carton Qty.</b>	2000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Stud Mount
<b>Height (imperial)</b>	0.25 "
<b>Height (metric)</b>	6.30 mm
<b>Length (imperial)</b>	8.3 "
<b>Length (metric)</b>	212.0 mm
<b>Max. Bundle Diameter (imperial)</b>	1.97 "
<b>Max. Bundle Diameter (metric)</b>	50.0 mm
<b>Min. Tensile Strength (imperial)</b>	80 lbs
<b>Min. Tensile Strength (metric)</b>	355 N
<b>Stud Diameter (imperial)</b>	0.31 "
<b>Stud Diameter (metric)</b>	8.0 mm
<b>Width (imperial)</b>	0.70 "
<b>Width (metric)</b>	17.75 mm

