

TECHNICAL DATA SHEET

Part No. 157-00343
Article No. 157-00343
Type T80ROSLPSB10U



One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 4.6 (PA46)
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Brown (BN)
Pkg. Qty.	3500
Carton Qty.	2500
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.28 "
Height (metric)	7.0 mm
Length (imperial)	8.5 "
Length (metric)	215.9 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	80 lbs
Min. Tensile Strength (metric)	355 N
Stud Diameter (imperial)	0.39 "
Stud Diameter (metric)	10.0 mm
Width (imperial)	0.82 "
Width (metric)	20.8 mm

