

TECHNICAL DATA SHEET

Part No. 157-00460
Article No. 157-00460
Type T80ROSLPSB5-6U



One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2500
Carton Qty.	2500
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.25 "
Height (metric)	6.30 mm
Length (imperial)	8.2 "
Length (metric)	208.3 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	80 lbs
Min. Tensile Strength (metric)	355 N
Stud Diameter (imperial)	0.20 ", 0.24 "
Stud Diameter (metric)	5.0 mm, 6.0 mm
Width (imperial)	0.56 "
Width (metric)	14.22 mm

