

TECHNICAL DATA SHEET

Part No. 157-00506
Article No. 157-00506
Type T50ROSFTQM6



HellermannTyton Blind Hole Mount Cable Tie for threaded holes offers an easy-to-use method for bundling and affixing cables. The one-piece mount offers a low insertion force and aggressively resists pull off, for secure attachment to panel holes with thicknesses from 0.02" to 0.28" or threaded blind holes. The disc on top of the mount covers the hole and minimizes ingress of water and debris.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000 Pieces
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.54 "
Height (metric)	13.8 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Length 2 (imperial)	0.64 "
Length 2 (metric)	16.13 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222.4 N
Mounting Hole Diameter (metric)	M6
Panel Thickness (imperial)	0.13 - 0.28 "
Panel Thickness (metric)	3.25 - 7.0 mm
Thickness (imperial)	0.06 "
Thickness (metric)	1.5 mm
Width (imperial)	0.20 "
Width (metric)	5.08 mm

RoHS