

TECHNICAL DATA SHEET

Part No. 157-00516
Article No. 157-00516
Type T50ROSFTM6SO25B



Offset cable ties route and position bundles away from a mounting hole. Rigid offset bar eliminates potential bending of wire or cables once installed. Multiple offset distances and fir tree sizes cover the majority of industry offset applications. The tie strap's outside serration design provides a smooth surface to protect soft bundles. HellermannTyton's one-piece mounting ties offer a complete solution by both bundling and mounting. Their ideal combination of high-specification materials and superior design suit the needs of complex applications.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	3000
Carton Qty.	3000 Pieces
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.86 "
Height (metric)	21.8 mm
Length (imperial)	9.1 "
Length (metric)	230.0 mm
Length 2 (imperial)	0.98 "
Length 2 (metric)	25.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222.4 N
Mounting Hole Diameter (imperial)	0.24 "
Mounting Hole Diameter (metric)	M6
Offset Length (imperial)	0.98 "
Offset Length (metric)	25.0 mm
Panel Thickness (imperial)	0.02 - 0.20 "
Panel Thickness (metric)	0.6 - 5.5 mm
Width (imperial)	0.75 "
Width (metric)	4.6 mm

