

TECHNICAL DATA SHEET

Part No. 157-00519
Article No. 157-00519
Type T50ROSFT612.5SO



One-piece stand-off cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. Stand-off feature positions bundles above a mounting hole. The disc prevents rattling in high-vibration applications and protects against debris ingress.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	3000
Carton Qty.	3000 Pieces
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.60 "
Height (metric)	16.1 mm
Length (imperial)	9.2 "
Length (metric)	234.2 mm
Length 2 (imperial)	0.49 "
Length 2 (metric)	12.5 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222.4 N
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Offset Length (imperial)	0.49 "
Offset Length (metric)	12.5 mm
Panel Thickness (imperial)	0.02 - 0.24 "
Panel Thickness (metric)	0.6 - 6.0 mm
Thickness (metric)	1.5 mm
Width (imperial)	0.20 "
Width (metric)	5.1 mm

