

TECHNICAL DATA SHEET

Part No. 161-62001
Article No. 161-62001
Type HWPP25



The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

Material	Polypropylene (PP)
Operating Temperature	-60 °C to +110 °C
Melting Point	+284 °F (+140 °C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10.0 ft
Carton Qty.	10
Customs Number	3926909988

Max. Bundle Diameter (imperial)	1.06 "
Max. Bundle Diameter (metric)	26.92 mm
Min. Bundle Diameter (imperial)	0.91 "
Min. Bundle Diameter (metric)	23.11 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25.0 mm
Reel Length (imperial)	10.0 ft
Reel Length (metric)	3.05 m
Wall Thickness (imperial)	0.041 "
Wall Thickness (metric)	1.05 mm

