

TECHNICAL DATA SHEET

Part No. 161-63403
Article No. 161-63403
Type HWPVAV025



The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

Material	Polyamide 6 V0 (PA6V0)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Melting Point	+248 °F (+120 °C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	3926909988

Max. Bundle Diameter (imperial)	1.06 "
Max. Bundle Diameter (metric)	27.0 mm
Min. Bundle Diameter (imperial)	0.91 "
Min. Bundle Diameter (metric)	23.0 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25.0 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.48 m
Wall Thickness (imperial)	0.041 "
Wall Thickness (metric)	1.05 mm

HF ✓ RoHS ✓

EN 45545-2

