

TECHNICAL DATA SHEET

Part No. 161-64006
Article No. 161-64006
Type HWCLIP20



The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size. Different cable sizes can be bundled together, organized and protected flexibly and efficiently.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Melting Point	+284 °F (+140 °C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use

Description	Accessory Clip
Max. Bundle Diameter (imperial)	0 "
Min. Bundle Diameter (imperial)	0 "
Nominal Diameter (imperial)	0.75 "
Nominal Diameter (metric)	20.0 mm
Pkg. Qty.	50

HF ✓

RoHS ✓