

# TECHNICAL DATA SHEET

**Part No.** 161-64112  
**Article No.** 161-64112  
**Type** HWPP8



The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

|                              |                                   |
|------------------------------|-----------------------------------|
| <b>Material</b>              | Polypropylene (PP)                |
| <b>Operating Temperature</b> | -76°F to +230°F (-60°C to +110°C) |
| <b>Melting Point</b>         | +284 °F (+140 °C)                 |
| <b>Flammability</b>          | UL 94 HB                          |
| <b>Halogen Free</b>          | Yes                               |
| <b>UV Resistant</b>          | No                                |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use        |
| <b>Color</b>                 | Black (BK)                        |
| <b>Pkg. Qty.</b>             | 1                                 |
| <b>Carton Qty.</b>           | 1                                 |
| <b>Customs Number</b>        | 3926909988                        |

|                                        |          |
|----------------------------------------|----------|
| <b>Max. Bundle Diameter (imperial)</b> | 0.36 "   |
| <b>Max. Bundle Diameter (metric)</b>   | 9.14 mm  |
| <b>Min. Bundle Diameter (imperial)</b> | 0.31 "   |
| <b>Min. Bundle Diameter (metric)</b>   | 7.87 mm  |
| <b>Nominal Diameter (imperial)</b>     | 0.31 "   |
| <b>Nominal Diameter (metric)</b>       | 8.0 mm   |
| <b>Reel Length (imperial)</b>          | 100.0 ft |
| <b>Reel Length (metric)</b>            | 30.48 m  |
| <b>Wall Thickness (imperial)</b>       | 0.0295 " |
| <b>Wall Thickness (metric)</b>         | 0.75 mm  |

HF✓

RoHS✓

**ECE R-118**