

TECHNICAL DATA SHEET

Part No. 161-64507
Article No. 161-64507
Type HWPP30



The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

Material	Polypropylene (PP)
Operating Temperature	-76°F to +230°F (-60°C to +110°C)
Melting Point	+284 °F (+140 °C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	3926909988

Max. Bundle Diameter (imperial)	1.26 "
Max. Bundle Diameter (metric)	32.0 mm
Min. Bundle Diameter (imperial)	1.14 "
Min. Bundle Diameter (metric)	29.0 mm
Nominal Diameter (imperial)	1.25 "
Nominal Diameter (metric)	30.0 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.48 m
Wall Thickness (imperial)	0.05 "
Wall Thickness (metric)	1.30 mm

HF✓

RoHS✓

ECE R-118