

TECHNICAL DATA SHEET

Part No. 164-41008
Article No. 164-41008
Type HelaDuct Flex40



HelaDuct Flex provides an extremely flexible method of routing wires in restricted-space applications. Smooth, overlapping, circular finger pattern reduces wire abrasion and eliminates the need for a separate cover in order to maintain wires when installed at angles greater than 90 degrees. Quick and easy inspection, access and removal of wires reduces installation and maintenance time. Available with adhesive foam strip for temporary positioning or non-adhesive back.

Fixation Method	Screw Mounting
Length (imperial)	19.7 "
Length (metric)	500 mm
Width (imperial)	1.77 "
Width (metric)	45.0 mm

Material	Polypropylene (PP)
Operating Temperature	-4°F to +158°F (-20°C to +70°C)
Flammability	UL 94 V-0 (excluding adhesive)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	24
Carton Qty.	24
Customs Number	3925900000

