

TECHNICAL DATA SHEET

Part No. 166-11809
Article No. 166-11809
Type HG-DC0500



A standard-weight corrugated conduit with two slit openings that eases installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. PA6 material is highly resistant to solvents and oils, and offers UV and abrasion resistance.

Material	Polyamide 6 (PA6)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	EN IEC 61386
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	164.0 ft
Carton Qty.	10
Customs Number	3926909988

Inner Diameter (imperial)	0.55 "
Inner Diameter 2 (metric)	13.9 mm
Inside Bend Radius (imperial)	4.73 "
Inside Bend Radius (metric)	120 mm
Length (imperial)	164.0 ft
Length (metric)	50 m
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	21 mm
Outside Diameter (imperial)	0.84 "
Outside Diameter (metric)	21.2 mm

