

TECHNICAL DATA SHEET

Part No. 166-90104
Article No. 166-90104
Type HG050-S-0500



HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Flammability	UL 94 V-2
Halogen Free	Yes
IP-Rating	IP66
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10
Carton Qty.	50
Customs Number	3926909988

Length (imperial)	1.73 "
Length (metric)	44 mm
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	21 mm
Outside Diameter (imperial)	1.26 "
Outside Diameter (metric)	32 mm

