

TECHNICAL DATA SHEET

Part No. 166-90131
Article No. 166-90131
Type PSR100-90-1000



Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 V-2
Halogen Free	Yes
IP-Rating	IP65
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10
Carton Qty.	50
Customs Number	3926909988

Length (imperial)	2.91 "
Length (metric)	74 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	32 mm
Outside Diameter (imperial)	1.89 "
Outside Diameter (metric)	48 mm

