

TECHNICAL DATA SHEET

Part No. 166-90182
Article No. 166-90182
Type PACC1250



Conduit Clips clamp onto corrugated conduits and tubing to secure. Nylon material resists corrosion and chemicals. Conduit clips can also be used on C-shaped DIN rails.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10
Carton Qty.	50
Customs Number	3926909988

Description	HelaGuard PACC Conduit Clip, 1.25" Dia
Height (imperial)	2.36 "
Height (metric)	60 mm
Width (metric)	15 mm

HF✓

RoHS✓