

TECHNICAL DATA SHEET

Part No. 166-90220
Article No. 166-90220
Type PSR0380



A lightweight tubing with a smooth inside bore, made of a spiral reinforced PVC material that provides high flexibility. This tubing is well-suited for protecting wire and cable bundles in extremely tight spaces. UV resistant. Use with HelaGuard Non-Metallic Compression Fittings to create an enclosed system.

Material	Polyvinylchloride (PVC)
Operating Temperature	-4°F to +158°F (-20°C to +70°C)
Flammability	EN IEC 61386
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	3926909988

Inner Diameter (imperial)	0.48 "
Inner Diameter 2 (metric)	12 mm
Inside Bend Radius (imperial)	0.99 "
Inside Bend Radius (metric)	25 mm
Length (imperial)	100.0 ft
Length (metric)	30.5 m
Nominal Diameter (imperial)	0.38 "
Nominal Diameter (metric)	16 mm
Outside Diameter (imperial)	0.65 "
Outside Diameter (metric)	16.5 mm

